



# User Guide

rev. 2021/12



Fully 3d printable

## Mitsubishi A6M2 Zero

scale 1:12, wingspan 1000 mm / 39.4 inch



## A6M2 Zero

### fully printable R/C plane for your desktop 3Dprinter


Fully 3D printable RC model of the Japanese attack plane, specially designed to meet ACES and EPA aircombat requirements, but also as a cheap and easy to build RC model for everyday flying. Many scale details such as armament or airframe plating encourages to create realistic paint jobs. This plane has been designed for printing from [PolyLight 1.0 LW-PLA](#) active foaming filament, that allow even the small printed planes to be as light as any other RC plane building technique. Get ready for battle with this great performing flying legend!

**The first fully printable** airplane files prepared for your 3Dprinter, with flight characteristics, comparable or even superior to classic build model airplane. This is not a dream, now you can print this HI-TECH at home. Simply download and print the whole plane or spare parts anytime you need just for a cost of filament only about \$12

**Extensive hi-tech 3d structural reinforcement** making the model very rigid while maintaining a lightweight airframe and exact airfoil even it's just a plastic. This perfect and exact 3d structure is possible only thanks to additive 3dprinting technology. So welcome to the 21st century of model flying and be the first at your airfield.

**Easy to assembly**, you don't need any extra tools or hardware, just glue printed parts together and make pushrods for control surfaces. The rest of the assembly is very easy. Simply add brushless motor, ESC, servos and radio system. Don't worry, detailed step by step PDF/VIDEO is included.

You'll get a superb performing airplane with highly efficient powerplant capable of flying 7+ minutes at full throttle and speeds exceeding 80 kph. Low stall speed is achieved for easy landing on the other hand.



## General specifications (HP setup):


Wingspan:	1000 mm / 39.4 inch
Length:	726 mm / 28.5 inch
Height:	188 mm / 7.4 inch
Wing area:	18,3 dm <sup>2</sup> / 1.96 square feet
Wing loading:	31 g/dm <sup>2</sup> / 15.3 oz/square feet
Center of gravity:	at the wing spar (60 mm from the leading edge)
Airfoil:	LHK508 modified by 3DLabPrint
Print weight (LW PLA):	224 g / 7.90 oz
Empty weight (w/o battery):	380 g / 13.40 oz
Takeoff weight (3s 1300 lipo):	500 g / 17.63 oz
Max takeoff weight:	700 g / 24.70 oz
Never exceed speed, VNE:	110 km/h / 62 mph
Design maneuvering speed, VA:	50 km/h / 31 mph
Stall speed, VS:	15 km/h / 9.4 mph


## Recommended setup

Motor:	Leopard LC2830 980KV (for 3-4S setup)
ESC:	20A/3-4S
Propeller:	two blade GWS 9 x 7,5 (ugly orange)
Battery:	1500/4S printed PET motor mount

## Performance measurement

Max speed VH (level flight):	105 km/h – 56.7kn – 65.2mph with GWS 9x7,5
Rate of climb:	20 m/s (5 373 ft/min) with GWS 9x7,5
Flight time (3s 1300mAh/full):	7:30 with GWS 9x7,5






## Mitsubishi A6M2 Zero (rei-shiki-kanjō-sentōki), History

The Mitsubishi A6M „Zero“ was a long-range carrier-based fighter aircraft formerly manufactured by Mitsubishi Aircraft Company, a part of Mitsubishi Heavy Industries, and operated by the Imperial Japanese Navy from 1940 to 1945. The A6M was designated as the Mitsubishi Navy Type 0 carrier fighter.

The Zero is considered to have been the most capable carrier-based fighter in the world when it was introduced early in World War II, combining excellent maneuverability and very long range. The Imperial Japanese Navy Air Service also frequently used it as a land-based fighter.

In early combat operations, the Zero gained a reputation as a dogfighter,[3] achieving an outstanding kill ratio of 12 to 1, but by mid-1942 a combination of new tactics and the introduction of better equipment enabled Allied pilots to engage the Zero on generally equal terms. During the final phases WWII, it was also adapted for use in kamikaze operations. Japan produced more Zeros than any other model of combat aircraft during the war.




## Included:

### 1. 3MF 3D files (primary)

#### Used instead of STL files

3mf files can be used instead of standard STL files, but also include information about slicing in the new version of **Prusa Slicer (since version 2.4)**. Open them directly in the Prusa Slicer as a project or import to the slicer of your choice. The files contain settings for printing on a direct drive printer with dimensions 200x200x200 mm, that can be further adapted to suit your printer. The generic settings are compatible with Prusa MK2/3/3S printers.



### 2. Factory files for Simplify3D slicer

contains all the necessary settings to slice the models along with suggested bed layout. We're using PRUSA i3 ORIGINAL printers so you may need to adjust the basic printing parameters to match your printer or use these files as a start point for you.

### 3. Printing Guide in our Help Section

Apart from this userguide, please see the Printing Guide for [PrusaSlicer](#), [Simplify3D](#) or [Cura](#) to find some Tips and Advice for airplane printing (Thin Wall Printing). **Remember: We use 0 retraction and 0.4-0.5 flow with LW-PLA.**

### 4. Gcodes







Basic Gcodes prepared for direct use, as universal as possible. Should work on i3 style printers, Give it a try, but we can't guarantee it will work on your printer. Wall thickness should be 0.60-0.67mm.

## 5. Scale markings PDF


You could print and cut the PDF in scale from thin self adhesive advertisement foil and place it on the model as needed.

# A1-191 A1-191 才7-150 才7-150


神風  
神風




A6M2 Zero  
3D  
LabPrint




## A6M2 Zero



Wing area: 18,3 dm<sup>2</sup> / 1.96 square feet



Length: 726 mm / 28.5 inch



Wing span: 1000 mm / 39.4 inch



## Step By Step PDF/VIDEO userguide


1. Choose airplane at [www.3DLabprint.com](http://www.3DLabprint.com), visit our [Facebook](#) for latest info.



Basic requirments for A6M2 Zero are 200/200/195 mm volume, nozzle 0.4mm recommended (0.35 or 0.5mm alternatively). Heated bed recommended. Designed to be printed with [Polylight LW-PLA filament](#) by 3DLabPrint. Contact: [support@3dlabprint.com](mailto:support@3dlabprint.com)

## 2. Create account, download


You will receive download link to all the zipped files to your email right after the checkout (please check your spam folder if not). If you are logged in with your account while purchasing the model, you will find the download link in your account's Downloads section on our website. Please contact [support@3dlabprint.com](mailto:support@3dlabprint.com) if you have trouble getting the files.



## 3. Prepare Gcodes


option A Gcodes:

if your printer is i3 comptabile you can use [prepared gcodes](#) directly. Just save them to the SD card and let the 3d printer do it's job. HE temperature is set to 240°C so the layers fuse together well, you can adjust speed and temperature only through your printer's LCD. If these Gcodes does not work for you, please proceed to the next options.



### option B Factory files Simplify3D:

We prepared all you need in these files (FFF process settings, parts layout on bed, etc...) You can use these settings as a start point. Adjust according to your need (adapt for your printer), print single parts and so on... Most 3d printers should work just with these settings, but please go through the settings and amend if necessary, we are not liable for any damage resulting from using our settings. If this still does not work for you, please proceed to the next option.




### option C Prusa Slicer 3mf files (recommended)

Please follow the guide in the Help section of our website about [Prusa Slicer setup](#). At the time of publishing this guide you need to **download the latest 2.4-beta version** from the [Prusa Slicer GitHub](#) as previous stable version doesn't support the Even/Odd slicing mode yet. Don't worry, it won't interfere with your installed stable version as it lives in a separate workplace.

Drag and drop the 3mf file to the Prusa Slicer window and open it as a Project. It will create a Generic 3DLabPrint printer, printing profile and materials. Please use these as a starting point instead of your printer profiles provided by your printer manufacturer. Strong thin-wall printing is a different discipline than printing Benchys what are the stock profiles usually optimized for. Once you tweak your profiles (retractions, etc.) you can easily switch the profile everytime you open the 3mf file. All the slicing tweaks, such as added top/bottom layers etc. are stored in the models below, so it won't be overwritten.

**Remember: We are using 0.5 multiplier and 0 retraction with LW-PLA.**



### option D CURA or MatterControl


MatterControl and CURA are free and provide satisfactory results. The airframe is still strong enough, but don't expect the best quality. Both slicers lacks some very useful features, and finer settings, like multiple processes according to Z height, retraction options, layer start, etc.

Please try to find the best extrusion multiplier and temperature for good weight and best possible layer bonding. Look at parts weight list for proper multiplier settings.

As a starting point you can use our predefined CURA or MC slicer setting file - see below (always adapt it for your printer, change build volume, filament diameter, etc...

according to your printer!!!)

Please check our [CURA guide](#) on the website for the latest basic profile. Please visualise our presliced gcodes to see how the result should look like and try to achieve the same in your slicer. **Remember: We are using 0.5 extrusion multiplier and 0 retraction with LW-PLA.**



## 4. Print it

Save the Gcodes to the SD card and insert into your printer. Prepare your printer and start printing, we prefer to use SD card rather than direct USB connection. Scaling the model will lead to unusable result!

you will need: LW-PLA filament - ([Polylight LW-PLA](#))  
3DLac, Strong hair spray, PEI or your favorite adhesive bed surface  
Razor blade

AND... please watch our VideoGuides:



## Basic Tips and Advice

While standard PLA filament could be used, this plane has been designed to be printed from foaming LW-PLA that means about 50% weight reduction on printed parts.

Please Experiment with temperature and extrusion multiplier (0.60-0.67mm Wall thickness). Hotend temperature is very important (220° up to 260° celsius). The temperature determines, how much the LW-PLA foams while printing. Cranking up temperature means, you can go lower on multiplier as the material will gain on volume. Turn OFF cooling fan for better layer adhesion (HE fan should be ON). We don't need it for thin wall printing. Heated bed is very recommended, 55-60° Celsius (to prevent warping ends).

Price of the LW-PLA may look a bit steep at first glance, but since we're using 50% less material thanks to the foaming feature, the cost difference is not so high as it looks.

Please see the [Printing Guide \(Help Section\)](#):

## Enjoy the fun together!

A6M2 Zero is the next of new LW Planes series designed for easy and cheap flying. The build is simple even for a beginner. It's very low weight, easy assembly and fantastic flight characteristics makes this model an ideal plane for beginner RC pilots.

Very suitable for dads and kids. Children will learn some modern building skills and technology and most of all have fun. This is the reason, why every dad should have a 3D printer at home.


This model has been completely designed with the new [PolyLight LW-PLA](#) material in mind.

Parts printed from this LW-PLA are light, easily sanded and glued together. This model requires only about 220 g of this material, that means it's a very cheap build. In case of accident, parts can be easily reprinted with just a filament cost.

We've been testing this material for half a year before this plane was released... The material is using an active foaming technology to achieve lightweight, low density PLA parts. At around 230°C this material will start foaming, increasing its volume by nearly 3 times.

All parts of this plane should be printed from LW-PLA except the cowling motor mount and el. Arm.

**Possibly A6M2 Zero can be printed from normal PLA but the plane will be too heavy for relaxed flying. Standard PLA printed model therefore could not be recommended for beginners. You should use heavier battery also to compensate Center of Gravity of the plane in this case.**



## weights of printed parts

fuselage	LW PLA g
cowling (PLA)	19 g
F1	23 g
F2	16 g
F3	15 g
F4	13 g
fuselage cover 1	2,2 g
fuselage cover 2	3,2 g
fuselage cover 3	7,1 g
cover arm (PLA)	2,8 g
wing	
wing L1	21 g
wing L2	12 g
wing L3	10 g
wing L4	2 g
wing R1	21 g
wing R2	12 g
wing R3	10 g
wing R4	2 g
aileron L1	4 g
aileron L2	3,5 g
aileron L3	4,5 g
aileron R1	4 g
aileron R2	3,5 g
aileron R3	4,5 g
tail	
stabiliser L1	5,9 g
stabiliser L2	2 g
stabiliser R1	5,9 g
stabiliser R2	2 g
elevator L1	4,8 g
elevator L2	0,5 g
elevator R1	4,8 g
elevator R2	0,5 g
elevator arm (PLA)	3 g
rudder	7,3 g
accessories	
motor mount (PETG)	11 g
spinner (PLA)	6 g
<b>all printed parts</b>	<b>269,5 g</b>

## How to print PolyLight LW-PLA?

The basic print setup is almost the same as we use for standard PLA. The only difference is in extrusion multiplier set to 0.5 and turning off the retractions completely.

This results in parts with half the weight and still suitable mechanical properties, this model is designed mainly in VASE mode, even that expect some stringing inside and outside in some impossible spots. Of course you can try to tweak the retractions for less stringing inside the parts, but there's a high risk of clogging the nozzle or throat. Increasing the retraction distance above 1 mm is not recommended at all and leads to nozzle clogs caused by foaming. Cleaning the hairy, but functional parts after printing with retractions completely disabled seems to be more efficient method. The nozzle is permanently pressurized and you don't need to worry about print failures. This method works fine even for bowden printers.

Extrusion multiplier 0,5 has been tested for easy print with massive weight saving around 50%. Feel free to experiment with extrusion multiplier and temperatures at will for the best results on your printer. This airplane is designed for **0.60-0.67mm** Wall thickness.

Cosmetic issues of the prints are easily fixed with snap knife or sand paper, as the LW is easily sanded and cut.



## 5. Assembly of printed parts



### 5.1 Wing assembly A6M2 Zero

Glue wing parts L1-L4 perfectly together. The new 3D LabPrint lock system will help you. Repeat for the right side. Glue both halves of the wing together. Use the CA glue, (position locks and wing pins will help you to align the parts), and use activator to speed up the glue curing. Press in and glue a piece of PolyAir, PLA or 1.5 mm carbon rod into the top and bottom opening to create a wing spar and improve the rigidity of the wing.

On a flat surface glue the ailerons L1-L3 and repeat for the right side. Use a filament or suitable 0,8mm - 1,5mm carbon rod as a hinge for the ailerons. Just slide it in, there's no need to glue the hinge for easy aileron or servo replacement. Wall thickness should be 0.60-0.67

[Video guide A6M2 ZERO Wing Assembly](#)

you will need: [CA Glue - medium](#) + [Activator for CA Glue](#)  
[PolyAir](#) or PLA filament (alt. carbon, fiberglass or steel wire)  
 Snap knife, SandPaper Some cloth for wiping CA glue...



## 5.2.1 Fuselage assembly A6M2 Zero

You can use snap knife for cleaning the surface of printed parts, but mostly it is not necessary. Glue fuselage parts F1-F4 with CA glue together. The new 3DLabPrint lock system will help you.

Check the alignment of F4 part compared to the wing before glueing. Do not glue rudder part before tail and elevator assembly. Use any hot tool to remove the unnecessary material from F4 tail part for the elevator arm.


Insert two 110 mm long 3 mm diameter carbon rods making a rubber band wing holders. No need to glue it for easy replacement. Wall thickness should be 0.60-0.67.

For fuselage cover arm use a ball pen spring. Put it to the part 2 and glue with part 1 together.


**NOTE: Don't glue the rudder tailpart yet !!! (proceed to the next step for elevator and stabilizer assembly)**

[See video guide A6M2 ZERO Fusselage Assembly](#)

you will need: [CA Glue - medium](#) + [Activator for CA Glue](#)  
 Snap knife, SandPaper Some cloth for wiping CA glue...  
 BallPen Spring



ball pen spring




## 5.2.2 Fuselage tail - elevator pushrods and servos

Glue L1 and L2 parts of the stabilizer and elevator. The profile is symmetric, so the left and right sides are identical. Glue the stabilizers perfectly perpendicular to the fuselage. Assemble both sides of the elevator with the elevator control lever on a flat surface. Make a Z bend on the elevator 0,8 mm pushrod wire. Using hot tool cut loose the hinge of the elevator on the F4 part of the fuselage and mount the elevator assembly to the stabilizer using the 0,8 - 1,2 mm carbon rod or steel wire. Elevator should move freely controlled by the pushrod and servo. Check the functionality of the elevator assembly carefully and finally glue in the rear rudder part. Wall thickness should be 0.60-0.67

you will need: [CA Glue medium viscosity+ activator](#)  
 0,8 - 1 mm steel wire for elevator pushrod  
 Polyair or PLA filament for aileron hinge  
 Snap knife, SandPaper Some cloth for wiping CA glue...

[Video guide A6M2 ZERO Tail Assembly](#)



elevator arm  
normal PLA!




## 6. Servo installation

Cut loose the servo holder ears on aileron servos. Install the prepared servos to wing servo bays. Use a 1mm steel wire with Z bends as a linkage between the servos and aileron control horns. Elevator servo will be fixed by screws directly to the fuselage.

### [Video guide A6M2 ZERO Servos](#)

you will need:      3x [HXT900](#), or similar 23x12x26 mm  
 Snap knife, [Z pliers](#)  
[CA Glue](#) + [activator](#) or Hot Glue



## 7. Motor & ESC & battery holder

Fix the battery by velcro tape and mount it in the front of the fuselage, find the perfect balance and CG position by moving it. Mount the motor using 4x M3 screws and nuts to the printed universal motor holder 16 x 19mm. For long motors you can flip the holder to the front. Glue universal motor mount with motor into the fuselage in right position.

### [Video guide A6M2 ZERO Motor Setup](#)

you will need:  
 4x M3/8mm screws + washers  
 Velcro tape

## LW planes setup (230W)

Motor:            any [2830 size motor](#) for 3S Li-Pol up to 70grams  
 ESC:             any [20A/3s Brushless Speed Controller](#) + connector [XT60](#)  
 Propeller:       GWS 9 x 7,5 (ugly orange) or [9x6](#)  
 Battery:         any [1500mAh / 3s](#), 140-160g



## 8. Final assembly/setting

Refer to your R/C system userguide for setup information.


### [Video guide A6M2 ZERO Final Setting](#)

you will need:      Your own Rx/Tx system (refer to your R/C system userguide for setup)  
                              4x rubber bands


Install your receiver, connect battery, setup servos and etc. with your transmitter, check servo position, then install propeller, the **supplied spinner** guarantees proper cooling of the motor and mount.

**Make sure the battery is positioned properly and secured with wing battery holder, if battery moves during flight it can shift the center of gravity backwards and aircraft will become uncontrollable! Never set ESC with propeller installed, this could be very dangerous!**

### aileron



### elevator



## 9. Go flying

Pre-flight check **center of gravity is very important** (move it 5mm forward for the first flights), battery properly charged, ailerons and elevator deflection check, your own flying skills or RC simulator training ...

### [Flyght video of A6M2 Zero](#)



## 10. Pilots Please Attention!

For the first flights we recommend setting the center of gravity to around 5 mm forward of the CG tag - nose heavy, this increases the stability (you can use heavier battery). Increasing expo settings on your transmitter for elevator and ailerons to 80 % calms response from your stick inputs. Also you can decrease elevator and ailerons deflection to calm down the plane. Make sure the battery is well fixed in proper position. If it moves during flight it will cause shifting of CoG aft and will result in uncontrollable flight behavior.

After gaining some confidence you can balance the plane to the Center of Gravity marks and set Expos to 60 % as shown in the video/instructions... this gains back extra maneuverability.

**Never fly aft positioned Center of gravity.**

Please, use these files only for your own purpose, do not redistribute or publish. Thank you very much.  
Enjoy your flight.



## Shopping list A6M2 ZERO:

Printing material:	0,25 kg of <a href="#">Polylight LW-PLA</a> a few of <a href="#">PolyAir</a> PLA or PETG filament
Motor:	any <a href="#">2830 size motor</a> for 3S Li-Pol with weight up to 70g
Propeller:	GWS 9 x 7,5 (ugly orange) or any <a href="#">9x6</a>
ESC:	any <a href="#">20A/3s Brushless Speed Controller</a> + connector <a href="#">XT60</a>
Battery:	any <a href="#">1500mAh / 3s</a> , 140-160g
Servos:	3x <a href="#">HXT900</a> , or similar 23x12x26 mm
Glue:	<a href="#">CA Glue - medium</a> <a href="#">Activator for CA Glue</a>
Other:	0.75m of 0.8-1.0 mm pushrod wire 4x M3/8mm screws + washers, velcro tape, 4x rubber bands